

Outside Microm. Anvil Extension Collar

Item number: 105-420

Images



Description

This Outside Micrometer comes with Extension Anvil Collars.

It offers you the following benefits:


- The collars have a stable and rugged yet lightweight tube construction, and are ideal for large micrometers.
- The 50 mm spindle stroke gives you extended range compared to standard spindle types.
- Anvil collars extend the measuring range even further.
- The setting standards supplied cover the whole measuring range.

Features

Model:	OMS2-1600P
Digital/Analog:	Analog
Delivered:	Including box, with spanner, setting standard (4 pcs.), 50/100 mm extension collar
Inch-Metric:	Metric
Measuring spindle:	With spindle lock, $\varnothing 8$ mm, spindle pitch 0,5 mm
Range:	1,400/1,600 mm
Scale:	Thimble and sleeve satin chrome finish, $\varnothing 21$ mm

Graduation:	0,01 mm
Limit of error:	±28 µm
Spindle feed error:	6 µm
Flatness:	1,3 µm
Parallelism:	18 µm
Measuring face:	Carbide-tipped, micro-lap finish
Measuring force:	5-10 N
Extension collar:	50/100 mm
Remarks:	With workpiece stop 100 mm adjustable
Mass:	12.6 kg

Dimensions



L: 1625 mm

a: 800 mm

Accessories

Standard accessories:

Micrometer Setting Standard

Length: 1400mm

Art No. 167-380

Suggested retail price: 810.00 €*



Micrometer Setting Standard

Length: 1450mm

Art No. 167-382

Suggested retail price: 837.00 €*



Micrometer Setting Standard

Length: 1500mm

Art No. 167-384

Suggested retail price: 867.00 €*



Micrometer Setting Standard

Length: 1550mm

Art No. 167-386

Suggested retail price: 893.00 €*

