

Outside Microm. Anvil Extension Collar

Item number: 105-422

Images



Description

This Outside Micrometer comes with Extension Anvil Collars.

It offers you the following benefits:


- The collars have a stable and rugged yet lightweight tube construction, and are ideal for large micrometers.
- The 50 mm spindle stroke gives you extended range compared to standard spindle types.
- Anvil collars extend the measuring range even further.
- The setting standards supplied cover the whole measuring range.

Features

Model:	OMS2-2000P
Digital/Analog:	Analog
Delivered:	Including box, with spanner, setting standard (4 pcs.), 50/100 mm extension collar
Inch-Metric:	Metric
Measuring spindle:	With spindle lock, $\varnothing 8$ mm, spindle pitch 0,5 mm
Range:	1,800/2,000 mm
Scale:	Thimble and sleeve satin chrome finish, $\varnothing 21$ mm

Graduation:	0,01 mm
Limit of error:	±33 µm
Spindle feed error:	6 µm
Flatness:	1,3 µm
Parallelism:	22 µm
Measuring face:	Carbide-tipped, micro-lap finish
Measuring force:	5-10 N
Extension collar:	50/100 mm
Remarks:	With workpiece stop 100 mm adjustable
Mass:	15.8 kg

Dimensions



L: 2025 mm

a: 1000 mm

Accessories

Standard accessories:

Micrometer Setting Standard

Length: 1800mm

Art No. 167-396

Suggested retail price: 1,042.00 €*



Micrometer Setting Standard

Length: 1850mm

Art No. 167-398

Suggested retail price: 1,067.00 €*



Micrometer Setting Standard

Length: 1900mm

Art No. 167-400

Suggested retail price: 1,106.00 €*



Micrometer Setting Standard

Length: 1950mm

Art No. 167-402

Suggested retail price: 1,130.00 €*

