


Range:	68 - 72 "
Scale:	Thimble and sleeve satin chrome finish, ø21 mm
Graduation:	0,001"
Limit of error:	±0,0015"
Spindle feed error:	0.0003 inch
Flatness:	0,000052"
Parallelism:	0.00079"
Measuring face:	Carbide-tipped, micro-lap finish
Measuring force:	5-10 N
Extension collar:	2"
Remarks:	With workpiece stop 100 mm adjustable
Mass:	14.9 kg

Dimensions



L: 1825 mm

a: 900 mm

Accessories

Standard accessories:

Micrometer Setting Standard

Length: 68"

Art No. 167-432

Suggested retail price: 979.00 €*


Micrometer Setting Standard

Length: 70"

Art No. 167-434

Suggested retail price: 1,018.00 €*
