

Contact Point Series 526

Item number: 10AAP248F

Images



Description

Split-ball probes 0,95-1,15 mm up to 6,7-7,3 mm range are protected by a diamond-like DLC coating.

Split-ball probes 7-18 mm are hard chrome plated


DLC Black Diamond:

- Extremely high wear protection, due to low frictional resistance
- Safety due to high hardness and resistance
- Safety due to sustained accuracy and precision

Features

Range:	2.75 - 3.25 mm
Marking on the measuring head (engraved):	3
Remarks:	Fitting on 526-163-20, 526-162-20

Dimensions



A: 22.5 mm

Remarks: () 526-152-20, 526-153-20