

## Contact Point Series 526

Item number: 10AAP249F

### Images



### Description

Split-ball probes 0,95-1,15 mm up to 6,7-7,3 mm range are protected by a diamond-like DLC coating.

Split-ball probes 7-18 mm are hard chrome plated

DLC Black Diamond:

- Extremely high wear protection, due to low frictional resistance
- Safety due to high hardness and resistance
- Safety due to sustained accuracy and precision

### Features

<b>Range:</b>	6.2 - 6.8 mm
<b>Marking on the measuring head (engraved):</b>	6.5
<b>Remarks:</b>	Fitting on 526-153-20, 526-152-20

### Dimensions

