

3 Flute V-Anvil Micrometer

Item number: 114-106

Images



Description

This V-Anvil Micrometer helps you measure cutting tools and taps.

It offers the following benefits:

- It measures the outside diameter of cutting tools (such as taps, reamers, end mills) which have three or five flutes.
- V-anvils with a centreline groove are available for measuring the pitch diameter of taps by the single-wire method.

Features

Digital/Analog:	Analog
Inch-Metric:	Metric
Range:	70 - 85 mm
Graduation:	0,01 mm
Max. Permissible Error J MPE:	$\pm 7 \mu\text{m}$
Delivered:	Including box, spanner, setting standard
Anvil:	Without groove
Measuring face:	Prism angle 60°/108°
Measuring spindle:	With spindle lock, $\varnothing 6,35$ mm, spindle pitch 0,75 mm
Scale:	Thimble and sleeve satin chrome finish, $\varnothing 18$ mm
Measuring force:	5 - 10 N
Setting standard:	167-332 $\varnothing 70$ mm
Mass:	910 g

Accessories

Optional accessories:

Promotion!



Micrometer Stand, Adjustable Angle Type

for Micrometer 0-100mm/0-4"

Art No. 156-101-10

Promo price: **56.00 €***

Suggested retail price: ~~70.00 €*~~

Standard accessories:



Setting Standard V-Anvil Micrometer

70mm

Art No. 167-332

Suggested retail price: **299.00 €***