

3 Flute V-Anvil Micrometer

Item number: 114-108

Images



Description

This V-Anvil Micrometer helps you measure cutting tools and taps.


It offers the following benefits:

- It measures the outside diameter of cutting tools (such as taps, reamers, end mills) which have three or five flutes.
- V-anvils with a centreline groove are available for measuring the pitch diameter of taps by the single-wire method.

Features

Digital/Analog:	Analog
Delivered:	Including box, spanner, setting standard
Inch-Metric:	Metric
Range:	100 - 115 mm
Graduation:	0,01 mm
Max. Permissible Error J MPE:	±8 µm
Anvil:	Without groove
Measuring face:	Prism angle 60°/108°
Measuring spindle:	With spindle lock, ø6,35 mm, spindle pitch 0,75 mm
Scale:	Thimble and sleeve satin chrome finish, ø18 mm
Measuring force:	5 - 10 N
Setting standard:	167-334 ø 100 mm
Mass:	1480 g

Dimensions



a: 84.1 mm

Accessories

Optional accessories:



Micrometer Stand

for Micrometer 100-300mm/5-12"

Art No. 156-102

Suggested retail price: 632.00 €*

Standard accessories:



Setting Standard V-Anvil Micrometer

100mm

Art No. 167-334

Suggested retail price: 856.00 €*