

Tube Micrometer

Item number: 115-313

Images



Description

A Mitutoyo non-digital tube micrometer equipped with a cylindrical anvil on a post for making wall thickness measurements on tubes and pipes. A ratchet stop guarantees repeatable measurement.

Features

Digital/Analog:	Analog
Inch-Metric:	Inch
Range:	0 - 1 "
Graduation:	0,001"
Max. Permissible Error J MPE:	±0.00015"
Delivered:	Including box, spanner
Flatness:	0.000024"
Measuring face:	Spindle and anvil: carbide-tipped, micro-lap finish (115-1xx, 115-2xx) spindle: carbide-tipped, micro-lap finish anvil: hardened steel (115-3xx)
Anvil / Spindle:	Type C, spherical pin D=4.7 mm/ flat spindle
Measuring spindle:	With spindle lock, ø6,35 mm, spindle pitch 0,5 mm
Scale:	Thimble and sleeve satin chrome finish, ø18 mm
Measuring force:	3 - 8 N
Mass:	180 g

Accessories

Optional accessories:



Micrometer Stand, 45° Angle Type

for Micrometer 0-50mm/0-2"
Art No. 156-105-10
Suggested retail price: 58.00 €*
Suggested retail price: 58.00 €*
Suggested retail price: 58.00 €*

Promotion!



Micrometer Stand, Adjustable Angle Type

for Micrometer 0-100mm/0-4"
Art No. 156-101-10
Promo price: **56.00 €***
~~Suggested retail price: 70.00 €*~~