

# Disc Micrometer, Hardened Steel Disks

Item number: 123-125

## Images



## Description

A Mitutoyo non-digital micrometer provided with disc-ended spindle and anvil to enable measurement of shrouded features, such as gear teeth. A ratchet stop guarantees repeatable measurement.

## Features

<b>Digital/Analog:</b>	Analog
<b>Inch-Metric:</b>	Inch
<b>Range:</b>	0 - 1 "
<b>Graduation:</b>	0,001"
<b>Max. Permissible Error J MPE:</b>	±0.0002"
<b>Delivered:</b>	Including box, spanner
<b>Flatness:</b>	0.00004"
<b>Parallelism:</b>	0.00016"
<b>Measuring face:</b>	Carbide-tipped (123-113, -114, -115, -116) or hardened steel spindle and anvil
<b>Measuring spindle:</b>	With spindle lock, $\varnothing 6,35$ mm, spindle pitch 0,5 mm
<b>Scale:</b>	Thimble and sleeve satin chrome finish, $\varnothing 18$ mm
<b>Measuring force:</b>	5 - 10 N
<b>Measurable module:</b>	0.5 - 6 mm
<b>Mass:</b>	200 g

## Dimensions

**L:** 37.5 mm  
**a:** 6 mm  
**b:** 14 mm  
**c:** 25 mm  
**d:** 20 mm

## Accessories

Optional accessories:



### Micrometer Stand, 45° Angle Type

for Micrometer 0-50mm/0-2"  
Art No. 156-105-10  
Suggested retail price: 58.00 €\*  
Suggested retail price: 58.00 €\*  
Suggested retail price: 58.00 €\*

Promotion!



### Micrometer Stand, Adjustable Angle Type

for Micrometer 0-100mm/0-4"  
Art No. 156-101-10  
Promo price: **56.00 €\*  
Suggested retail price: 70.00 €\***