

## Depth Stylus for Height Gauge

Item number: 12AAY599


### Images



### Description

Depth Stylus for Height Gauge for max. 70mm Depth


### Dimensions




### Accessories

Optional accessories:

#### Ball Probe Coaxial Type

D=1mm, 72mm Length  
Art No. 12AAF666  
Suggested retail price: 201.00 €\*  


#### Ball Probe Coaxial Type

D=2mm, 72mm Length  
Art No. 957261  
Suggested retail price: 114.00 €\*  


### Ball Probe Coaxial Type

D=2mm, Ruby, 72mm Length  
Art No. 12AAF667  
Suggested retail price: 319.00 €\*  

---



### Ball Probe Coaxial Type

D=3mm, 72mm Length  
Art No. 957262  
Suggested retail price: 120.00 €\*  

---



### Ball Probe Coaxial Type

D=4mm, 76mm Length  
Art No. 957263  
Suggested retail price: 132.00 €\*  

---



### Ball Probe, Coaxial Type

D=10mm  
Art No. 12AAB552  
Suggested retail price: 185.00 €\*  

---



### Ball Probe Coaxial Type

D=10mm, 82mm Length  
Art No. 12AAF668  
Suggested retail price: 230.00 €\*  

---



### **Ball Probe Coaxial Type**

D=10mm, 120mm Length  
Art No. 12AAF669  
Suggested retail price: 251.00 €\*  

---



### **Disk Probe Coaxial Type**

D=5mm, 75mm Length  
Art No. 12AAF670  
Suggested retail price: 222.00 €\*  

---



### **Disk Probe Coaxial Type**

D=10mm, 59mm Length  
Art No. 12AAF671  
Suggested retail price: 177.00 €\*  

---



### **Disk Probe Coaxial Type**

D=14mm, 59mm Length  
Art No. 957264  
Suggested retail price: 234.00 €\*  

---



### **Disk Probe Coaxial Type**

D=20mm, 48mm Length  
Art No. 957265  
Suggested retail price: 293.00 €\*  

---



### Disk Stylus, Coaxial Type

D=25mm, 99,5mm Length  
Art No. 12AAAY598  
Suggested retail price: 193.00 €\*  

---



### Ball Probe Eccentric Type

D=1mm  
Art No. 12AAF672  
Suggested retail price: 179.00 €\*  


---



### Ball Probe Eccentric Type

D=2mm  
Art No. 12AAF673  
Suggested retail price: 240.00 €\*  

---



### Ball Probe Eccentric Type

D=4mm  
Art No. 12AAA788  
Suggested retail price: 81.00 €\*  

---



### Ball Probe Eccentric Type

D=6mm  
Art No. 12AAA789  
Suggested retail price: 87.00 €\*  

---



### **Stylus, Eccentric Type**

D=5mm, 130mm Length  
Art No. 12AAY597  
Suggested retail price: 519.00 €\*  

---



### **CMM Stylus Adapter M2**

Art No. 226117  
Suggested retail price: 57.00 €\*  

---



### **CMM Stylus Adapter M3**

Art No. 226118  
Suggested retail price: 57.00 €\*  

---



### **Depth Stylus for Height Gauge**

for max. 70mm Depth  
Art No. 12AAY599  
Suggested retail price: 135.00 €\*  

---




### **Depth Stylus for Height Gauge**

for max. 150mm Depth  
Art No. 12AAY600  
Suggested retail price: 155.00 €\*  

---




### Depth Stylus for Height Gauge

for max. 300mm Depth  
Art No. 12AAY601  
Suggested retail price: 155.00 €\*  



---

### Depth Stylus for Height Gauge

Offset Type, for max. 70mm Depth, D=2mm Ball  
Art No. 12AAY602  
Suggested retail price: 231.00 €\*  



---

### Depth Stylus for Height Gauge

Offset Type, for max. 150mm Depth,  
D=2mm Ball  
Art No. 12AAY603  
Suggested retail price: 250.00 €\*  



---

### Depth Stylus for Height Gauge

Offset Type, for max. 300mm Depth,  
D=2mm Ball  
Art No. 12AAY604  
Suggested retail price: 250.00 €\*  


---

### Depth Stylus for Height Gauge

Offset Type, for max. 70mm Depth, D=4mm Ball  
Art No. 12AAY605  
Suggested retail price: 213.00 €\*  


---

### Depth Stylus for Height Gauge

Offset Type, for max. 150mm Depth,  
D=4mm Ball

Art No. 12AAY606

Suggested retail price: 213.00 €\*  

---



### Depth Stylus for Height Gauge

Offset Type, for max. 300mm Depth,  
D=4mm Ball

Art No. 12AAY607

Suggested retail price: 231.00 €\*  

---



### Extension Holder, 100mm

for Height Gauge

Art No. 12AAY595

Suggested retail price: 270.00 €\*  

---



### Extension Holder, 200mm

for Height Gauge

Art No. 12AAY596

Suggested retail price: 310.00 €\*  

---



### Depth Probe for Height Gauge

90mm Reach

Art No. 12AAC072

Suggested retail price: 201.00 €\*  

---





### Indicator Holder LH-600

For 8mm Stem  
Art No. 12AAA792  
Suggested retail price: 134.00 €\*  

---



### Probe Extension Holder, Height Gauge

85mm  
Art No. 12AAA793  
Suggested retail price: 134.00 €\*  

---



### Tapered Measuring Insert

D=22mm  
Art No. 12AAC073  
Suggested retail price: 161.00 €\*  

---



### Setting Block Linear Height/QM-Height

Probe Calibration and Taper Probe  
Art No. 12AAA787  
Suggested retail price: 287.00 €\*  

---



### Cylindrical Probe

D=10mm  
Art No. 12AAB136  
Suggested retail price: 292.00 €\*  

---



### Stylus Kit M3 for Linear Height

with Holder, 5 Probes, 2 Extensions, 1 Dowel-key  
Art No. K650986  
Suggested retail price: 452.00 €\*



### Power Cable CEE Type

for Europe (except UK)  
Art No. 02ZAA021  
Suggested retail price: 7.70 €\*



### Receipt Printer for LH-600F/FG

CEE Type  
Art No. 12AAY483  
Suggested retail price: 1,499.00 €\*



### Printer Paper

Serie 518, LH-600, 10 Rolls  
Art No. 12AAN052  
Suggested retail price: 118.00 €\*



### U-WAVE-T Transmitter Mounting Plate

for LH-600F/FG  
Art No. 12AAY486  
Suggested retail price: 51.00 €\*

## USB Cable

A-Type 2m  
Art No. 12BAF812  
Suggested retail price: 18.50 €\*  
Photo Not Available

Promotion!



### Connection Cable D for U-WAVE

Flat 10-Pin Type  
Art No. 02AZD790D  
Promo price: **63.90 €\***  
Suggested retail price: 98.00 €\*

Promotion!



### Connection Cable SF for U-WAVE

for U-WAVE-T and Instruments with  
Digimatic S1 Interface  
Art No. 02AZG011  
Promo price: **109.00 €\***  
Suggested retail price: 131.00 €\*

Promotion!



### USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, Flat 10-Pin  
Type  
Art No. 06AFM380D  
Promo price: **98.90 €\***  
Suggested retail price: 124.00 €\*



### Digimatic Cable, Straight, 1m

Digimatic/Digimatic 2/Digimatic S1 Interface  
Art No. 06AGL011  
Suggested retail price: 79.00 €\*  
Photo Not Available



### Digimatic Cable, Straight, 2m

Digimatic/Digimatic 2/Digimatic S1 Interface  
Art No. 06AGL021  
Suggested retail price: 84.00 €\*  
~~129.00 €\* (crossed out)~~

Promotion!



### USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2/Digimatic  
S1 Interface  
Art No. 06AGQ001F  
Promo price: 129.00 €\*  
Suggested retail price: 164.00 €\*  
~~164.00 €\* (crossed out)~~



### AC-Adapter, DC 6V 2A

CEE version Germany (Europe)  
Art No. 06AGZ369D  
Suggested retail price: 85.00 €\*  
~~129.00 €\* (crossed out)~~



### AC-Adapter, 6V 2A

Korea  
Art No. 06AGZ369E  
Suggested retail price: 85.00 €\*  
~~129.00 €\* (crossed out)~~



### Digimatic Cable, Flat 10-Pin Type

1 m  
Art No. 936937  
Suggested retail price: 57.00 €\*  
~~129.00 €\* (crossed out)~~



## Digimatic Cable, Flat 10-Pin Type

2 m

Art No. 965014

Suggested retail price: 72.00 €\*  
~~72.00 €\*~~

Promotion!



## USB Input Tool Interface Box

Digimatic/Digimatic 2/Digimatic S1 Interface

Art No. 264-020

Promo price: **209.00 €\***   
~~259.00 €\*~~

Suggested retail price: 259.00 €\*  
~~259.00 €\*~~

Promotion!



## U-WAVE-T, IP67 Type

Wireless Transmitter

Art No. 02AZD730G

Promo price: **129.00 €\***   
~~187.00 €\*~~

Suggested retail price: 187.00 €\*  
~~187.00 €\*~~

Promotion!




## U-WAVE-T, Buzzer Type

Wireless Transmitter

Art No. 02AZD880G

Promo price: **129.00 €\***   
~~187.00 €\*~~

Suggested retail price: 187.00 €\*  
~~187.00 €\*~~



## U-WAVE Transmitter Mounting Plate

for QM-Height

Art No. 02AZE990

Suggested retail price: 43.00 €\*  
~~43.00 €\*~~

Promotion!



### U-WAVE-R Wireless Receiver

Based on IEEE802.15.4 (2,4 GHz)

Art No. 02AZD810D

Promo price: **249.00 €\***

Suggested retail price: ~~371.00 €\*~~

Promotion!



### U-WAVE fit Bluetooth, IP67 Type

Wireless Transmitter for  
Micrometer/Indicator

Art No. 264-626

Promo price: **139.00 €\***

Suggested retail price: ~~185.00 €\*~~

Promotion!



### U-WAVE fit Bluetooth, Buzzer Type

Wireless Transmitter for  
Micrometer/Indicator

Art No. 264-627

Promo price: **139.00 €\***

Suggested retail price: ~~185.00 €\*~~



### USB Cable 1m, DP-1VA to PC etc.

USB Type A to Micro USB Type B Plug

Art No. 06AFZ050

Suggested retail price: **21.00 €\***