


Tubular Inside Micrometer

Item number: 133-147

Images



Description

This is a standard single rod type inside micrometer (individual unit), with the following features:

- Standard single rod.
- Carbide measuring faces.

Features

Inch-Metric:	Metric
Digital/Analog:	Analog
Range:	150 - 175 mm
Graduation:	0.01 mm
Max. Permissible Error J MPE:	$\pm 5 \mu\text{m}$
Scale:	Thimble and sleeve satin chrome finish, $\text{\O}18 \text{ mm}$
Measuring spindle:	With spindle lock (except 50-75 mm), spindle pitch 0,5 mm
Measuring face:	Carbide tipped
Measuring method:	2-point
Delivered:	Including box and spanner
Mass:	170 g

Dimensions

