

# Tubular Inside Micrometer

Item number: 133-150

## Images



## Description

This is a standard single rod type inside micrometer (individual unit), with the following features:

- Standard single rod.
- Carbide measuring faces.

## Features

<b>Inch-Metric:</b>	Metric
<b>Digital/Analog:</b>	Analog
<b>Range:</b>	225 - 250 mm
<b>Graduation:</b>	0.01 mm
<b>Max. Permissible Error J MPE:</b>	$\pm 6 \mu\text{m}$
<b>Scale:</b>	Thimble and sleeve satin chrome finish, $\varnothing 18 \text{ mm}$
<b>Measuring spindle:</b>	With spindle lock (except 50-75 mm), spindle pitch 0,5 mm
<b>Measuring face:</b>	Carbide tipped
<b>Measuring method:</b>	2-point
<b>Delivered:</b>	Including box and spanner
<b>Mass:</b>	210 g

## Dimensions

