

Tubular Inside Micrometer

Item number: 133-156

Images



Description

This is a standard single rod type inside micrometer (individual unit), with the following features:

- Standard single rod.
- Carbide measuring faces.

Features

Digital/Analog:	Analog
Inch-Metric:	Metric
Range:	375 - 400 mm
Graduation:	0.01 mm
Max. Permissible Error J MPE:	$\pm 8 \mu\text{m}$
Scale:	Thimble and sleeve satin chrome finish, $\varnothing 18 \text{ mm}$
Measuring spindle:	With spindle lock (except 50-75 mm), spindle pitch 0,5 mm
Measuring face:	Carbide tipped
Measuring method:	2-point
Delivered:	Including box and spanner
Mass:	315 g

Dimensions

