


Tubular Inside Micrometer with Extension

Item number: 140-164

Images



Description

A Mitutoyo inside micrometer covering a range of measurement by using a set of interchangeable extension tubes that can be used singly or in combination. The micrometer head is satin-chrome finished.

Features

Inch-Metric:	Inch
Digital/Analog:	Analog
Range:	40 - 200 "
Measuring span:	2"
Graduation:	0.001"
Limit of error:	$\pm(0,00035+0,00005 \times \text{number of rods} + 0,00005(\text{max. measurement length}/2))"$
Scale:	Thimble and sleeve satin chrome finish, $\varnothing 21$ mm
Measuring spindle:	Spindle pitch 0,635 mm
Measuring face:	Carbide
Extension rods:	8 (2, 4 (2 pcs.), 8, 20, 40" (3 pcs.))
Delivered:	Including box, spanner, extension rods (8 pcs.), micrometer head
Spindle feed error:	0.0003 inch
Mass:	9000 g

Dimensions



Spare parts

Consumable spares:



Extension Rod 50mm, for Series 140

Art No. 04GZA394
Suggested retail price: 172.00 €*



Extension Rod 100mm, for Series 140

Art No. 04GZA396
Suggested retail price: 221.00 €*



Extension Rod 200mm, for Series 140

Art No. 04GZA398
Suggested retail price: 316.00 €*



Extension Rod 500mm, for Series 140

Art No. 04GZA400
Suggested retail price: 535.00 €*



Extension Rod 1000mm, for Series 140

Art No. 04GZA402
Suggested retail price: 800.00 €*
