

Dial Gauge, Flat Back, ANSI/AGD Type

Item number: 1411AB

Images



Description

Compact Type, Small Diameter - Inch

This is a compact, inch dial indicator with a bezel Ø 40 mm. It offers you the following benefits:

- It is ideal for use in applications where space is limited.
- Green limit markers are a standard accessory.

Features

Digital/Analog:	Analog
Inch-Metric:	Inch
Range:	0,25 "
Range per rev.:	0,1"
Dial reading:	0-50-0
Delivered:	With certificate of inspection, bezel clamp
Graduation:	0,001"
H MPE (Hysteresis):	0,0002"
R MPE (Repeatability):	±0,0002"
MPE first one revolution:	±0,001"
MPE first 2 1/2 revolutions:	±0,001"
Type:	ANSI/AGD Standard
Measuring force:	0,4-1,4 N

Stem:	9.52 mm / 0.375"
Contact point:	Carbide tipped, thread: 4-48UNF
Balanced dial:	Yes
Continuous dial:	Yes
Mass:	70 g

Dimensions

A: 1.28 inch

B: 1.87 inch

C: 1.57 inch

D: 0.59 inch

E: 3/4 inch

F: 0.5 inch

G: 0.58 inch

H: 1.5 inch

I: 0.26 inch

Accessories

Optional accessories:



Limit Hands (Green) 2 pcs.

Dial Indicator Series 1, Test Indicator
Art No. 21AAB363

Price on application



Spindle Lifting Lever

for S-Type and A-Type Serie 1
Art No. 902100

Price on application



Spindle Lifting Cable

for Indicator, L=500mm

Art No. 21JZA295

Price on application



Spindle Lifting Cable with Auto Stop

for Indicator, L=300mm

Art No. 21JZA301

Price on application

Standard accessories:



Bezel Clamp for Dial Gauge

Series 1

Art No. 21RZA149

Price on application

Spare parts

Consumable spares:



Contact Element Ball Point, 4-48UNF

1/4" Length, Carbide, Inch

Art No. 21BZB005

Suggested retail price: 13.30 €*

