

Caliper Jaw Inside Micrometer

Item number: 145-194

Images



Description


The Caliper Jaw Inside Micrometer offers you the following benefits:

- Carbide measuring faces
- A setting standard (optional) is needed to accurately set the micrometer to the reference point.

Features

Digital/Analog:	Analog
Inch-Metric:	Inch
Range:	1 - 2 "
Graduation:	0,001"
Max. Permissible Error J MPE:	±0.0003"
Scale:	Thimble and sleeve satin chrome finish, ø18 mm
Measuring spindle:	With spindle lock, spindle pitch 0,635 mm
Measuring face:	Carbide tipped
Measuring force:	1-6 N
Delivered:	Including box, spanner, setting standard is not included
Mass:	140 g

Dimensions



Accessories

Optional accessories:

Holder for Series 145

Art No. 300400

Price on application



Cap for Series 145

Art No. 300401

Price on application

