


## Caliper Jaw Inside Micrometer

Item number: 145-217

### Images



### Description


The Caliper Jaw Inside Micrometer offers you the following benefits:

- Carbide measuring faces
- A setting standard (optional) is needed to accurately set the micrometer to the reference point.

### Features


<b>Inch-Metric:</b>	Metric
<b>Digital/Analog:</b>	Analog
<b>Range:</b>	200 - 225 mm
<b>Graduation:</b>	0,01 mm
<b>Measuring force:</b>	1-6 N
<b>Max. Permissible Error J MPE:</b>	±11 µm
<b>Scale:</b>	Thimble and sleeve satin chrome finish, ø18 mm
<b>Measuring spindle:</b>	With spindle lock, spindle pitch 0,5 mm
<b>Measuring face:</b>	Carbide tipped
<b>Delivered:</b>	Including box, spanner, setting standard is not included
<b>Mass:</b>	310 g

### Dimensions



## Accessories

Optional accessories:



### Holder for Series 145

Art No. 300400

Price on application

### Cap for Series 145

Art No. 300401

Price on application

