

Micrometer Head, Ultra Small Type

Item number: 148-203-10

Images



Description

A small, non-digital Mitutoyo micrometer head with M6 clamp-nut stem and flat spindle tip.

Features

Digital/Analog:	Analog
Delivered:	In a paper box
Inch-Metric:	Metric
Range:	0 - 6.5 mm
Graduation:	0,01 mm
Max. Permissible Error J MPE:	±5 μm
Spindle end:	Flat
Spindle pitch:	0,5 mm
Stem Ø:	6 mm
Stem:	w/ clamp nut
Fixture thickness for clamp nut:	4 mm
Measuring face:	Hardened steel (> 60 HRC)
Mass:	10 g

Dimensions

