

Micrometer Head, Ultra Small Type

Item number: 148-207-10

Images



Description

A small, non-digital Mitutoyo micrometer head with M6 clamp-nut stem and spherically radiused spindle tip.

Features

Digital/Analog:	Analog
Delivered:	In a paper box
Inch-Metric:	Metric
Range:	0 - 6.5 mm
Graduation:	0.01 mm
Max. Permissible Error J MPE:	$\pm 5 \mu\text{m}$
Spindle end:	Spherical (SR3)
Spindle pitch:	0.5 mm
Stem \varnothing:	6 mm
Stem:	w/ clamp nut
Fixture thickness for clamp nut:	4 mm
Measuring face:	Hardened steel (> 60 HRC)
Mass:	10 g

Dimensions

