

Micrometer Head, Locking Screw Type

Item number: 148-222-10

Images



Description

These micrometer heads feature a knurled locking screw so you can lock the spindle in any position with the knurled locking screw.

Features

Digital/Analog:	Analog
Delivered:	In a paper box
Inch-Metric:	Metric
Range:	0 - 6.5 mm
Graduation:	0.01 mm
Max. Permissible Error J MPE:	±5 μm
Spindle end:	Spherical (SR3)
Spindle pitch:	0.5 mm
Stem Ø:	6 mm
Stem:	Plain
Measuring face:	Hardened steel (> 60 HRC)
Mass:	16 g

Dimensions

