

Micrometer Head, Locking Screw Type

Item number: 148-230-10

Images



Description

These micrometer heads feature a knurled locking screw so you can lock the spindle in any position with the knurled locking screw.

Features

Digital/Analog:	Analog
Delivered:	In a paper box
Inch-Metric:	Inch
Range:	0 - 0.25 "
Graduation:	0.001"
Max. Permissible Error J MPE:	±0.00025"
Spindle end:	Flat
Spindle pitch:	0.5 mm
Stem Ø:	0.25"
Stem:	Plain
Measuring face:	Hardened steel (> 60 HRC)
Mass:	16 g