

## Micrometer Head, Locking Screw Type

Item number: 148-231-10

### Images



### Description

These micrometer heads feature a knurled locking screw so you can lock the spindle in any position with the knurled locking screw.

### Features

<b>Digital/Analog:</b>	Analog
<b>Delivered:</b>	In a paper box
<b>Inch-Metric:</b>	Inch
<b>Range:</b>	0 - 0.25 "
<b>Graduation:</b>	0.001"
<b>Max. Permissible Error J MPE:</b>	±0.00025"
<b>Spindle end:</b>	Flat
<b>Spindle pitch:</b>	0.5 mm
<b>Stem Ø:</b>	0.25"
<b>Stem:</b>	w/ clamp nut
<b>Fixture thickness for clamp nut:</b>	4 mm
<b>Measuring face:</b>	Hardened steel (> 60 HRC)
<b>Mass:</b>	17 g