

Micrometer Head, Locking Screw Type

Item number: 148-327-10

Images



Description

These micrometer heads feature a knurled locking screw so you can lock the spindle in any position with the knurled locking screw.

Features

| | |
|---|------------------------------------|
| Digital/Analog: | Analog |
| Delivered: | In a paper box with spanner 301336 |
| Inch-Metric: | Inch |
| Range: | 0 - 0.25 " |
| Graduation: | 0.001" |
| Max. Permissible Error J MPE: | ±0.0001" |
| Spindle end: | Flat |
| Spindle pitch: | 0.5 mm |
| Stem Ø: | 0.375" |
| Stem: | w/ clamp nut |
| Fixture thickness for clamp nut: | 6 mm |
| Measuring face: | Hardened steel (> 60 HRC) |
| Mass: | 43 g |