

Micrometer Head, Short Thimble Type

Item number: 148-357-10

Images



Description

Short thimble type with thimble diameter options.

Features

Digital/Analog:	Analog
Delivered:	In a paper box
Inch-Metric:	Inch
Range:	0 - 0.5 "
Graduation:	0.001"
Max. Permissible Error J MPE:	±0,0001"
Spindle end:	Flat
Spindle pitch:	0,5 mm
Stem Ø:	0.375"
Stem:	Plain
Measuring face:	Hardened steel (> 60 HRC)
Thimble Ø:	0,59"
Mass:	35 g