

Micrometer Head, Small Standard Type

Item number: 148-814

Images



Description

A small, standard, non-digital Mitutoyo micrometer head with M9.5 clamp-nut stem and spherically radiused spindle tip.

Features

Digital/Analog:	Analog
Inch-Metric:	Inch
Range:	0 - 0.5 "
Graduation:	0.001"
Max. Permissible Error J MPE:	±0.0001"
Spindle end:	Spherical (SR4)
Spindle pitch:	0.5 mm
Stem Ø:	0.375"
Stem:	w/ clamp nut
Fixture thickness for clamp nut:	6 mm
Delivered:	In a paper box with spanner 301336
Measuring face:	Hardened steel (>60 HRC)
Mass:	45 g

Dimensions

