

# Micrometer Head, Small Standard Type

Item number: 148-834

## Images



## Description

This is a standard, small-sized micrometer head which offers you the following benefits:

- Plain stem and a flat or spherical spindle end
- Hardened steel measuring surface

## Features

|   |                                    |
|---|------------------------------------|
| <b>Digital/Analog:</b>                  | Analog                             |
| <b>Inch-Metric:</b>                     | Inch                               |
| <b>Range:</b>                           | 0 - 0.5 "                          |
| <b>Graduation:</b>                      | 0.001"                             |
| <b>Max. Permissible Error J MPE:</b>    | ±0.0001"                           |
| <b>Spindle end:</b>                     | Flat                               |
| <b>Spindle pitch:</b>                   | 0.5 mm                             |
| <b>Stem Ø:</b>                          | 0.375"                             |
| <b>Stem:</b>                            | w/ clamp nut                       |
| <b>Fixture thickness for clamp nut:</b> | 6 mm                               |
| <b>Special features:</b>                | Reverse reading                    |
| <b>Delivered:</b>                       | In a paper box with spanner 301336 |
| <b>Measuring face:</b>                  | Hardened steel (>60 HRC)           |
| <b>Mass:</b>                            | 45 g                               |

## Dimensions

