


Micrometer Head, Carbide Tipped Spindle

Item number: 149-831-10

Images



Description

This small micrometer head with tungsten carbide measuring surface offers you the following benefits:

- Stem with clamp nut and a flat or spherical spindle end
- Stem with carbide-tipped spindle

Features

Digital/Analog:	Analog
Delivered:	In a paper box
Inch-Metric:	Inch
Range:	0 - 0.5 "
Graduation:	0.001"
Max. Permissible Error J MPE:	±0.0001"
Spindle end:	Flat
Spindle pitch:	0,5 mm
Stem Ø:	375"
Stem:	Plain
Special features:	Reverse reading
Measuring face:	Carbide tipped (>90 HRA)
Mass:	55 g