

Micrometer Head, Medium-sized Standard

Item number: 150-207

Images



Description

A medium sized, standard, non-digital Mitutoyo micrometer head with M9.5 clamp-nut stem and flat tungsten-carbide spindle tip.

Features

Digital/Analog:	Analog
Inch-Metric:	Inch
Graduation:	0,001"
Max. Permissible Error J MPE:	±0.0001"
Range:	0 - 1 "
Spindle end:	Flat
Spindle pitch:	0,5 mm
Stem Ø:	0.375"
Stem:	w/ clamp nut
Fixture thickness for clamp nut:	11.5 mm
Delivered:	In a paper box with spanner 301336
Measuring face:	Carbide-tipped
Mass:	100 g

Dimensions

