

Micrometer Head, Medium-sized Standard

Item number: 150-214

Description

This is a standard, medium-size micrometer head that offers you the following benefits:

- Plain stem and a flat or spherical spindle end
- With carbide-tipped spindle

Features

Digital/Analog:	Analog
Delivered:	In a paper box with spanner 301336
Inch-Metric:	Inch
Graduation:	0,001"
Max. Permissible Error J MPE:	±0.0001"
Range:	0 - 1 "
Spindle end:	Flat
Spindle pitch:	0,5 mm
Stem Ø:	0.375"
Stem:	w/ clamp nut
Fixture thickness for clamp nut:	11.5 mm
Measuring face:	Carbide-tipped
Mass:	115 g

Dimensions

