

# Micrometer Head, Medium-sized Standard

Item number: 150-216

## Description

This is a standard, medium-size micrometer head that offers you the following benefits:

- Plain stem and a flat or spherical spindle end
- With carbide-tipped spindle

## Features

<b>Digital/Analog:</b>	Analog
<b>Delivered:</b>	In a paper box with spanner 301336
<b>Inch-Metric:</b>	Inch
<b>Graduation:</b>	0.0001"
<b>Max. Permissible Error J MPE:</b>	±0.0001"
<b>Range:</b>	0 - 1 "
<b>Spindle end:</b>	Flat
<b>Spindle pitch:</b>	0,5 mm
<b>Stem Ø:</b>	0.375"
<b>Stem:</b>	w/ clamp nut
<b>Fixture thickness for clamp nut:</b>	11.5 mm
<b>Special features:</b>	Graduation 0.0001"
<b>Measuring face:</b>	Carbide-tipped
<b>Mass:</b>	115 g

## Dimensions

