

Microm. Head, Heavy Duty, 8 mm Spindle

Item number: 151-212

Images



Description

These micrometer heads are a medium-sized, standard type. They offer the following benefits:

- 8 mm diameter spindle
- Extremely sturdy micrometer head with or without a ratchet.

Features

Digital/Analog:	Analog
Delivered:	In a paper box with spanner 200154
Inch-Metric:	Metric
Range:	0 - 25 mm
Graduation:	0.001 mm
Max. Permissible Error J MPE:	$\pm 2 \mu\text{m}$
Spindle end:	Flat
Spindle pitch:	0,5 mm
Stem \varnothing:	12 mm
Stem:	Plain
Special features:	Graduation 0.001 mm
Measuring face:	Carbide-tipped
Mass:	160 g

Dimensions

