

# Microm. Head, Heavy Duty, 8 mm Spindle

Item number: 151-213

## Images



## Description

These micrometer heads are a medium-sized, standard type. They offer the following benefits:

- 8 mm diameter spindle
- Extremely sturdy micrometer head with or without a ratchet.

## Features

<b>Digital/Analog:</b>	Analog
<b>Delivered:</b>	In a paper box with spanner 200154
<b>Inch-Metric:</b>	Metric
<b>Range:</b>	0 - 25 mm
<b>Graduation:</b>	0.01 mm
<b>Max. Permissible Error J MPE:</b>	±2 µm
<b>Spindle end:</b>	Flat
<b>Spindle pitch:</b>	0,5 mm
<b>Stem Ø:</b>	12 mm
<b>Stem:</b>	w/ clamp nut
<b>Fixture thickness for clamp nut:</b>	15.5 mm
<b>Measuring face:</b>	Carbide-tipped
<b>Mass:</b>	165 g

## Dimensions

