

Microm. Head, Heavy Duty, 8 mm Spindle

Item number: 151-244

Images



Description

These micrometer heads are a medium-sized, standard type. They offer the following benefits:

- 8 mm diameter spindle
- Extremely sturdy micrometer head with or without a ratchet.

Features

Digital/Analog:	Analog
Delivered:	In a paper box with spanner 200154
Inch-Metric:	Inch
Range:	0 - 0,1 "
Graduation:	0.0001"
Max. Permissible Error J MPE:	±0.0001"
Spindle end:	Flat
Spindle pitch:	0,5 mm
Fixture thickness for clamp nut:	15.5 mm
Special features:	w/o ratchet stop
Measuring face:	Carbide-tipped

Dimensions

