

Micrometer Head Non-rotating Spindle

Item number: 153-202

Images



Description

A non-digital, high-resolution Mitutoyo micrometer head with plain $\text{l}\approx 12\text{mm}$ stem and non-rotating spindle fitted with flat tungsten-carbide tip. Ratchet stop.

Features

Model:	MHK-25VR
Digital/Analog:	Analog
Inch-Metric:	Metric
Range:	0 - 25 mm
Graduation:	0,001 mm
Max. Permissible Error J MPE:	$\pm 3 \mu\text{m}$
Spindle end:	Flat
Spindle pitch:	0,5 mm
Stem \varnothing:	12 mm
Stem:	Plain
Special features:	Graduation with vernier
Delivered:	In a paper box with spanner 301336
Measuring face:	Carbide tipped
Mass:	125 g

Dimensions

