

Digital Micrometer Head

Item number: 164-163

Images



Description

A Mitutoyo digital, non-rotating spindle micrometer head with plain stem and flat spindle tip. The display is rotatable for viewing convenience. Digimatic data output.

Features

Digital/Analog:	Digital
Inch-Metric:	Metric
Range:	0 - 50 mm
Digital step:	0.001 mm
Max. Permissible Error J MPE:	±3 μm
Spindle end:	Flat
Spindle pitch:	0.5 mm
Stem Ø:	18 mm
Stem:	Flat
Delivered:	Including SR44 battery (2 pcs.), screwdriver
Remarks:	Non-rotating spindle
Display:	LCD, character Height 7.5 mm
Measuring face:	Carbide tipped
Data output:	Yes
Power supply:	2 batteries SR-44
Battery life:	Approx. 1.8 years
ABS / INC (INC ZERO):	Yes
Auto Power OFF after 20 min. non use:	Yes
Low voltage alarm:	Yes
2 x PRESET:	Yes
Counting direction switchable:	Yes
Mass:	490 g

Dimensions

Promotion!



U-WAVE-T, IP67 Type

Wireless Transmitter

Art No. 02AZD730G

Promo price: **129.00 €***

Suggested retail price: ~~187.00 €*~~

Promotion!



Connection Cable C for U-WAVE

Straight, with Data Button

Art No. 02AZD790C

Promo price: **72.00 €***

Suggested retail price: ~~105.00 €*~~

Spare parts

Consumable spares:



Battery SR44 1,5 V

Art No. 938882

Suggested retail price: 7.00 €*