


Steel Rule, Semi-Flexible Rule

Item number: 182-305

Images



Description

These are rigid and fully-flexible rules that offer you the following benefits:

- They have clear graduations on satin-chrome finish.
- The rules are stainless tempered.

Features

Inch-Metric:	Inch/Metric
Range:	0 - 12 "
Graduation:	1/16", 1/32", 1/64", 1 mm, 0,5mm
Accuracy:	±0,006"/ ±0,15 mm
Width:	0.625"
Thickness:	0,4 mm
Functions:	Semi-flexible rule Engraved on one side only