

# Digital Height Gauge Double Column

Item number: 192-673-10

## Images



## Description

A Mitutoyo digital height gauge, twin column design. Multi-functional type. Digimatic data output. An extensive range of accessories extends the application range.

## Features

<b>Model:</b>	HDM-40"AX
<b>Digital/Analog:</b>	Digital
<b>Range:</b>	0 - 40 "
<b>Digital step:</b>	0.0005/0.0002" or 0.01/0.005 mm
<b>Delivered:</b>	Including carbide tipped scriber, scriber clamp and SR44 battery
<b>Max. Permissible Error E MPE:</b>	$\pm 0,0025"/\pm 0,06$ mm
<b>Max. Permissible Error J MPE:</b>	$\pm 0,06$ mm/0,0025"
<b>Display:</b>	LCD, Character Height: 11 mm
<b>Max. response speed:</b>	500 mm/s
<b>ON/OFF:</b>	Yes
<b>ABS / INC (INC ZERO):</b>	Yes
<b>PRESET (2 values):</b>	Yes
<b>Touch-trigger probe:</b>	Yes
<b>Stylus tip diameter compensation:</b>	Yes
<b>DATA (output with cable) / HOLD (display value):</b>	Yes
<b>Low voltage alarm:</b>	Yes
<b><math>\pm</math>SWITCHING:</b>	Yes
<b>Mm / inch switching:</b>	Yes
<b>Inch-Metric:</b>	Inch/Metric
<b>Power supply:</b>	1 battery SR-44





## Digimatic Cable, Flat Straight Type

2 m  
Art No. 905409  
Suggested retail price: 44.00 €\*  
Promotion!



## USB Input Tool Direct (Digimatic to USB)

2m Cable, Digimatic/Digimatic 2, Flat Straight Type  
Art No. 06AFM380F  
Promo price: 98.00 €\*  
Suggested retail price: 124.00 €\*  
Promotion!



## U-WAVE-T, Buzzer Type

Wireless Transmitter  
Art No. 02AZD880G  
Promo price: 129.00 €\*  
Suggested retail price: 187.00 €\*  
Promotion!



## U-WAVE-T, IP67 Type

Wireless Transmitter  
Art No. 02AZD730G  
Promo price: 129.00 €\*  
Suggested retail price: 187.00 €\*  
Promotion!



## Connection Cable F for U-WAVE

Straight, without Data Button  
Art No. 02AZD790F  
Promo price: 68.00 €\*  
Suggested retail price: 98.00 €\*  
Promotion!

### **Holding Bar for Swivel Clamp**

6,25x12,7mm, 2" Length  
Art No. 953639  
Suggested retail price: 19.50 €\*  

---



### **Holding Bar for Swivel Clamp**

12,7x6,35mm, 4" Length  
Art No. 900306  
Suggested retail price: 17.30 €\*  

---



### **Swivel Clamp**

for D= 4/9,52mm, Dovetail  
Art No. 900322  
Suggested retail price: 26.50 €\*  

---



### **Depth Gauge Attachment**

for 12,7mm x 6,35mm  
Art No. 900878  
Suggested retail price: 59.00 €\*  

---



### **Center Master**

for 6,35x12,7mm  
Art No. 900581  
Suggested retail price: 161.00 €\*  

---





### Contact Sensor

for Height Gauges

Art No. 900872

Suggested retail price: 135.00 €\*

---

#### Standard accessories:



### Scriber Clamp

for 6,35x12,7mm Scriber

Art No. 901385

Suggested retail price: 23.80 €\*



### Carbide Tipped Scriber

6,35x12,7mm, 150mm Length

Art No. 905201

Suggested retail price: 137.00 €\*

---

#### Spare parts

---

#### Consumable spares:



### Battery SR44 1,5 V

Art No. 938882

Suggested retail price: 7.00 €\*

