

Dial Snap Gauge without Indicator

Item number: 201-158

Images



Description

A Mitutoyo dial snap gauge designed for quick GO/NG judgement of diameters of cylinders and shafts. Anvils are chamfered for easy workpiece insertion. The dial indicator is optional, enabling the user to choose from the wide range available to best suit the application.

Features

Digital/Analog:	Analog
Inch-Metric:	Inch
Range:	7 - 8 "
Delivered:	Including thermally insulating grip, workpiece stop
Anvil retracting stroke:	2 mm
Repeatability:	2 μm
Flatness:	1 μm
Parallelism:	0.0002"
Remarks:	For indicator with 9.52 mm stem
Measuring face:	Carbide-tipped, micro-lap finish (13.5x12 mm)
Measuring force:	12 - 18 N
Mass:	1200 g

Dimensions

Accessories

Optional accessories:



Dial Gauge, Flat Back, ANSI/AGD Type

One Revolution, Shock- & Dustproof, 0,06",
0,001"

Art No. 2978AB

Suggested retail price: **116.00 €***



Dial Gauge, Flat Back, ANSI/AGD Type

Jewelled Bearing, Shockproof, 0,025",
0,0001"

Art No. 2803AB-10

Suggested retail price: **140.00 €***



Dial Gauge, Flat Back, ANSI/AGD Type

0,5", 0,001"

Art No. 2415AB

Suggested retail price: **94.00 €***



Protector for Indicator (plastic cover)

Art No. 21DZA000

Suggested retail price: **14.50 €***

Standard accessories:



Dial Indicator, Flat Back, AGD/ANSI

0,5", 0,001"

Art No. 2415SB

Suggested retail price: 72.00 €*



Dial Indicator, Flat Back, AGD/ANSI

0.025", 0.0001", Jew. Bearing, Shockpr.

Art No. 2803SB-10

Suggested retail price: 103.00 €*



Protector for Indicator (plastic cover)

Art No. 21DZA000

Suggested retail price: 14.50 €*



Dial Indicator, Flat Back, AGD/ANSI

0.06", 0.001", One Revo., Dust/Shockproof

Art No. 2978TB

Suggested retail price: 79.36 €*