

Dial Gauge, Flat Back, ANSI/AGD Type

Item number: 2046A-01

Images



Features

Digital/Analog:	Analog
Inch-Metric:	Metric
Range:	10 mm
Range per rev.:	1 mm
Dial reading:	±0-100
Delivered:	With certificate of inspection, bezel clamp
Graduation:	0,01 mm
MPE any 1/10 revolution:	5 µm
MPE any 1/2 revolution:	9 µm
MPE any 1 revolution:	10 µm
MPE first one revolution:	±10 µm
MPE first 2 1/2 revolutions:	±10 µm
MPE > 2 1/2-10 revolutions:	±13 µm
H MPE (Hysteresis):	3 µm
R MPE (Repeatability):	±3 µm
Type:	ANSI/AGD Standard
Measuring force:	0,4-1,4 N
Stem:	9.52 mm / 0.375"
Contact point:	Carbide tipped, thread: 4-48UNF
Continuous dial:	Yes

Accessories

Optional accessories:



Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4
Art No. 21AZB195
Price on application



Spindle Lifting Lever

for Digital Indicator, A-Type Dial Indicator
Serie 2/3/4
Art No. 21EZA198
Price on application



Spindle Lifting Cable

for Indicator, L=500mm
Art No. 21JZA295
Price on application



Spindle Lifting Cable with
Auto Stop

for Indicator, L=300mm
Art No. 21JZA301
Price on application

Standard accessories:



Bezel Clamp for Dial Gauge

Inch, Series 2/3/4

Art No. 21RZA065

Suggested retail price: 5.00 €*

Spare parts

Consumable spares:



Contact Element Ball Point, 4-48UNF

1/4" Length, Carbide, Inch

Art No. 21BZB005

Suggested retail price: 13.30 €*
