

Dial Gauge, Flat Back, ANSI/AGD Type

Item number: 2119AB-11

Images



Features

Digital/Analog:	Analog
Inch-Metric:	Metric
Range:	5 mm
Range per rev.:	0,2 mm
Dial reading:	0-10-0
Delivered:	With certificate of inspection, bezel clamp
Graduation:	0,001 mm
MPE first one revolution:	±7 μm
MPE first 2 1/2 revolutions:	±7 μm
MPE > 2 1/2-10 revolutions:	±8 μm
MPE > 10-20 revolutions:	±10 μm
MPE > 20 revolutions:	±10 μm
H MPE (Hysteresis):	2.5 μm
R MPE (Repeatability):	±0.3 μm
Type:	ANSI/AGD Standard
Measuring force:	0,4-1,5 N
Stem:	9.52 mm / 0.375"
Contact point:	Carbide tipped, thread: 4-48UNF

Accessories

Optional accessories:



Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4

Art No. 21AZB195

Price on application



Spindle Lifting Lever

for Digital Indicator, A-Type Dial Indicator
Serie 2/3/4

Art No. 21EZA198

Price on application



Spindle Lifting Cable

for Indicator, L=500mm

Art No. 21JZA295

Price on application



Spindle Lifting Cable with Auto Stop

for Indicator, L=300mm

Art No. 21JZA301

Price on application

Standard accessories:



Bezel Clamp for Dial Gauge

Inch, Series 2/3/4

Art No. 21RZA065

Suggested retail price: 5.00 €*
Photo Not Available

Spare parts

Consumable spares:



Contact Element Ball Point, 4-48UNF

1/4" Length, Carbide, Inch

Art No. 21BZB005

Suggested retail price: 13.30 €* *incl. VAT