

Contact Point for Series 526

Item number: 21DAA603B

Images



Description

Split-ball probes 0,95-1,15 mm up to 6,7-7,3 mm range are protected by a diamond-like DLC coating.

Split-ball probes 7-18 mm are hard chrome plated

DLC Black Diamond:

- Extremely high wear protection, due to low frictional resistance
- Safety due to high hardness and resistance
- Safety due to sustained accuracy and precision

Features

Range:	4.2 - 4.8 mm
Marking on the measuring head (engraved):	4.5
Remarks:	Fitting on 526-153-20, 526-152-20

Dimensions

