

Dial Gauge, Flat Back, ANSI/AGD Type

Item number: 2805AB-10

Images



Description

Standard Type, Various Ranges, 0,0001" Graduation - Inch

- This is a standard, inch dial indicator. It offers you the following benefits:
- Bezel clamp and lifting lever (optional) can be attached to either right or left side. They can be easily installed and removed without tools.
 - No through screw holes on the frame and secure adhesion between the bezel and the crystal as well as the use of an O-ring prevents water or oil penetration.

Features

Digital/Analog:	Analog
Inch-Metric:	Inch
Range:	0,05 "
Range per rev.:	0.01 "
Dial reading:	0-5-0
Delivered:	With certificate of inspection, bezel clamp
Graduation:	0.0001"
H MPE (Hysteresis):	0,0001"
R MPE (Repeatability):	±0,00003"
MPE first one revolution:	±0,0001"
MPE first 2 1/2 revolutions:	±0,0001"
MPE > 2 1/2-10 revolutions:	±0,0002"

Type:	ANSI/AGD Standard
Measuring force:	0,4-2 N
Stem:	9.52 mm / 0.375"
Contact point:	Carbide tipped, thread: 4-48UNF
Balanced dial:	Yes
Continuous dial:	Yes
Shockproof:	Yes
Mass:	139 g

Dimensions

A: 1.86 inch

B: 2.04 inch

C: 2.24 inch

D: 0.71 inch

E: 3/4 inch

F: 0.54 inch

G: 0.38 inch

H: 2.05 inch

I: 0.30 inch

Accessories

Optional accessories:

Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4
 Art No. 21AZB195
Price on application

Spindle Lifting Lever

for Digital Indicator, A-Type Dial Indicator
 Serie 2/3/4
 Art No. 21EZA198
Price on application

Spindle Lifting Cable

for Indicator, L=500mm

Art No. 21JZA295

Price on application



Spindle Lifting Cable with Auto Stop

for Indicator, L=300mm

Art No. 21JZA301

Price on application



Standard accessories:

Bezel Clamp for Dial Gauge

Inch, Series 2/3/4

Art No. 21RZA065

Suggested retail price: 5.00 €*
Photo Not Available



Spare parts

Consumable spares:

Contact Element Ball Point, 4-48UNF

1/4" Length, Carbide, Inch

Art No. 21BZB005

Suggested retail price: 13.30 €*
Photo Not Available



