

## Digital Tubular Inside Micrometer (Pipe)

Item number: 339-301

### Images



Dust- and Water-Protected

www.tuv.com  
ID 0000021605



### Description

A Mitutoyo digital inside micrometer covering a range of measurement by using a set of interchangeable extension tubes that can be used singly or in combination. The micrometer head is satin-chrome finished.

### Features

<b>Model:</b>	IMJ-1000MJ
<b>Inch-Metric:</b>	Metric
<b>Digital/Analog:</b>	Digital
<b>Range:</b>	200 - 1,000 mm
<b>Measuring span:</b>	25 mm
<b>Digital step:</b>	0,001 mm
<b>Spindle feed error:</b>	3 $\mu$ m
<b>Limit of error:</b>	$\pm(3+\text{number of rods}+\text{max. measurement length}/50)$ $\mu$ m
<b>Power supply:</b>	1 battery SR-44
<b>Scale:</b>	Thimble and sleeve satin chrome finish, $\varnothing$ 18 mm





## Battery SR44 1,5 V

Art No. 938882

Suggested retail price: 7.00 €\*  

---