

Dial Gauge, Flat Back, ANSI/AGD Type

Item number: 3415AB

Images



Description

This is a standard, inch dial indicator. It offers you the following benefits:


- Large-diameter dial face $\varnothing = 78\text{ mm}$ for easy reading
- Supplied with limit markers and a bezel clamp as standard
- $0.001'' / 0.0001''$ graduation

Features

Digital/Analog:	Analog
Inch-Metric:	Inch
Delivered:	With certificate of inspection, bezel clamp
Range:	0,5 "
Range per rev.:	0,1"
Dial reading:	0-50-0
Graduation:	0.001"
H MPE (Hysteresis):	0,0002"
R MPE (Repeatability):	$\pm 0,0002''$
MPE first one revolution:	$\pm 0,001''$
MPE first 2 1/2 revolutions:	$\pm 0,001''$
MPE > 2 1/2-10 revolutions:	$\pm 0,001''$
Type:	ANSI/AGD Standard
Measuring force:	0,4-1,8 N

Mass:	244 g
Stem:	9.52 mm / 0.375"
Contact point:	Carbide tipped, thread: 4-48UNF
Balanced dial:	Yes
Continuous dial:	Yes

Dimensions



A: 2.07 inch

B: 2.89 inch

C: 3.07 inch

D: 0.7 inch

E: 3/4 inch

F: 0.5 inch

G: 0.86 inch

H: 2.8 inch

I: 0.35 inch

Accessories

Optional accessories:



Limit Hands (green) 2pcs

Dial Indicator Series 2/3/4
Art No. 21AZB195
Price on application

Standard accessories:



Bezel Clamp for Dial Gauge

Inch, Series 2/3/4
Art No. 21RZA065
Suggested retail price: 2.10 €*

Spare parts

Consumable spares:



Contact Element Ball Point, 4-48UNF

1/4" Length, Carbide, Inch

Art No. 21BZB005

Suggested retail price: 15.00 €* *incl. VAT