

## Digital Micrometer Head, 0-1"

Item number: 350-357-30

### Images



### Description

This Micrometer Head has a 25 mm range and a 10 mm stem, and offers the following benefits:

- You can integrate it into machinery and measuring instruments.
- Measurement values are clearly displayed in 0.001mm increments.
- Stem diameter: 10 mm.

### Features

<b>Digital/Analog:</b>	Digital
<b>Inch-Metric:</b>	Inch/Metric
<b>Range:</b>	0 - 1 "
<b>Digital step:</b>	0.00005"/0.001 mm
<b>Max. Permissible Error J MPE:</b>	±0.0001"
<b>Spindle end:</b>	Spherical (SR4)
<b>Stem Ø:</b>	0.375"
<b>Stem:</b>	Plain
<b>Delivered:</b>	Including spanner, SR44 battery
<b>Remarks:</b>	Without ratched stop
<b>Display:</b>	LCD, character Height 7.5 mm
<b>Measuring face:</b>	Carbide tipped
<b>Measuring spindle:</b>	With spindle lock, ø 6,35 mm
<b>Scale:</b>	Thimble and sleeve satin chrome finish
<b>Data output:</b>	Yes
<b>Power supply:</b>	1 battery SR-44
<b>Battery life:</b>	Approx. 2,4 years
<b>ABS / INC (INC ZERO):</b>	Yes
<b>Auto Power OFF after 20 min. non use:</b>	Yes

**Low voltage alarm:** Yes

**Function lock:** Yes

**HOLD:** Yes

**2 x PRESET:** Yes

**Mass:** 230 g

## Accessories

### Optional accessories:

Promotion!

Mitutoyo

MiCAT

the standard in world  
metrology software  
MeasurLink®

### USB-ITPAK Vers. 3.0

USB Dongle + Manual (Software available  
Online)

Art No. 06AGR543

Promo price: **268.00 €\***

Suggested retail price: ~~340.00 €\*~~



## Spare parts

### Consumable spares:



### Battery SR44 1,5 V

Art No. 938882

Suggested retail price: 7.00 €\*