

3-Point Internal Micrometer Holtest

Item number: 368-773

Images



Description

A non-digital Mitutoyo bore gauge. Hardened steel contact faces. A ratchet stop guarantees repeatable measurement.

Features

Inch-Metric:	Metric
Digital/Analog:	Analog
Range:	87 - 100 mm
Graduation:	0,005 mm
Max. Permissible Error J MPE:	$\pm 4 \mu\text{m}$

Scale: Thimble and sleeve satin chrome finish,
Up to 12 mm : Ø 17 mm
Over 12 mm : Ø 23 mm

Measuring spindle: Spindle pitch 0,5 mm


Measuring face: hardened steel
Taper: hardened steel

Measuring method: 3-point

Delivered: Including box, spanner, hex wrench,
certificate of inspection, without setting
ring

Mass: 570 g

Dimensions




a: 3.4 mm

b: 14 mm

L1: 150 - 163 mm

L2: 105 mm



a: 3.4 mm

b: 14 mm

L1: 150 - 163 mm

L2: 105 mm

Accessories

Optional accessories:



Holtest, Borematic Extension 150mm

for 50-300mm Measuring Range
Art No. 952623
Suggested retail price: 216.00 €*



Setting Ring 87mm

Steel
Art No. 177-318
Suggested retail price: 407.00 €*

Setting Ring 100mm

Steel

Art No. 177-296

Suggested retail price: 521.00 €*

