



# 2-Point Internal Micrometer

## Holtest Set

Item number: 368-906

### Images



### Description

This is a set of three-point and two-point internal micrometers that offers you the following benefits:

- Complete unit set.
- Carbide measuring surface (2-6 mm range).
- Titanium-coated measuring pins (>6 mm range) give you excellent durability and impact resistance.
- Delivered with setting rings and extension rod (>6 mm range).

### Features

<b>Digital/Analog:</b>	Analog
<b>Inch-Metric:</b>	Metric
<b>Range:</b>	2 - 3 mm
<b>Graduation:</b>	0,001 mm
<b>Individual ranges:</b>	2-2.5, 2.5-3 mm
<b>Scale:</b>	Thimble and sleeve satin chrome finish, Up to 12 mm : Ø 17 mm Over 12 mm : Ø 23 mm
<b>Measuring spindle:</b>	Spindle pitch 0,5 mm
<b>Measuring face:</b>	Tungsten carbide
<b>Measuring method:</b>	2-point
<b>Models included:</b>	368-001 / 368-002
<b>Setting rings included:</b>	ø2.5 mm (177-208)
<b>Delivered:</b>	Including box, hex wrench, certificate of inspection, setting ring (1 pcs.)
<b>Mass:</b>	310 g