

## 2-Point Internal Micrometer

### Holtest Set

Item number: 368-907

#### Images



#### Description

This is a set of three-point and two-point internal micrometers that offers you the following benefits:

- Complete unit set.
- Carbide measuring surface (2-6 mm range).
- Titanium-coated measuring pins (>6 mm range) give you excellent durability and impact resistance.
- Delivered with setting rings and extension rod (>6 mm range).

#### Features

|                                |  |
|--------------------------------|--|
| <b>Digital/Analog:</b>         | Analog   |
| <b>Inch-Metric:</b>            | Metric   |
| <b>Range:</b>                  | 3 - 6 mm   |
| <b>Graduation:</b>             | 0,001 mm   |
| <b>Individual ranges:</b>      | 3-4, 4-5, 5-6 mm   |
| <b>Scale:</b>                  | Thimble and sleeve satin chrome finish,<br>Up to 12 mm : Ø 17 mm<br>Over 12 mm : Ø 23 mm |
| <b>Measuring spindle:</b>      | Spindle pitch 0,5 mm   |
| <b>Measuring face:</b>         | Tungsten carbide   |
| <b>Measuring method:</b>       | 2-point  |
| <b>Models included:</b>        | 368-003 / 368-004 / 368-005  |
| <b>Setting rings included:</b> | ø4 mm (177-204)<br>ø5 mm (177-205)   |

**Delivered:**

Including box, hex wrench, certificate of inspection, setting rings (2 pcs.)

**Mass:**

505 g