

3-Point Internal Micrometer

Holtest Set

Item number: 368-911

Images



Description

This is a set of metric 3-point internal micrometers that offers you the following benefits:

- Stable measurement through automatic centering
- Carbide measuring surface (2-6 mm range)
- 2 setting rings and 1 extension

Features

Inch-Metric:	Metric
Digital/Analog:	Analog
Range:	6 - 12 mm
Graduation:	0,001 mm
Individual ranges:	6-8, 8-10, 10-12 mm
Scale:	Thimble and sleeve satin chrome finish, Up to 12 mm : Ø 17 mm Over 12 mm : Ø 23 mm
Measuring spindle:	Spindle pitch 0,5 mm
Measuring face:	Titanium coated tungsten carbide taper: tungsten carbide
Measuring method:	3-point
Models included:	368-161 / 368-162 / 368-163
Setting rings included:	ø8 mm (177-125) ø10 mm (177-126)
Delivered:	Including box, spanner (2 pcs.), hex wrench, certificate of inspection, setting rings (2 pcs.), extension rod
Mass:	180 g