

3-Point Internal Micrometer

Holtest Set

Item number: 368-912

Images



Description

This is a set of metric 3-point internal micrometers that offers you the following benefits:

- Stable measurement through automatic centering
- Carbide measuring surface (2-6 mm range)
- 1 setting ring and 1 extension

Features

Inch-Metric:	Metric
Digital/Analog:	Analog
Range:	12 - 20 mm
Graduation:	0,005 mm
Individual ranges:	12-16, 16-20 mm
Scale:	Thimble and sleeve satin chrome finish, Up to 12 mm : Ø 17 mm Over 12 mm : Ø 23 mm
Measuring spindle:	Spindle pitch 0,5 mm
Measuring face:	Titanium coated tungsten carbide taper: tungsten carbide
Measuring method:	3-point
Models included:	368-164 / 368-165
Setting rings included:	ø16 mm (177-177)
Delivered:	Including box, spanner (2 pcs.), hex wrench, certificate of inspection, setting ring (1 pcs.), extension rod
Mass:	280 g